


ORASCAN CA

CEILING ACCESSORY FOR ORASCAN

ASSEMBLY



1. Ceiling Frame (black)
2. Ceiling Accessory Base (white)
3. Light pipe support (black)
4. ORASCAN Module (without its standard base and cover)
5. Cover (white or black)




1. MOUNTING POSITION

The ORASCAN Ceiling Accessory must be installed within the following height and depth limits :

Ceiling Height [m]	Maximum door - middle of sensor distance [cm]
2.2	23 cm
2.5	30 cm
3	40 cm
Max 3.5	50 cm



2. CEILING PANEL CUTTING



3. INSTALLATION

